

| Order Code | Final drive | Type | Speed rpm |
|------------|-------------|------|-----------|
|------------|-------------|------|-----------|

|       |   |        |         |
|-------|---|--------|---------|
| 12100 | Accepts De Soutter acetabular reamer shells | MI-600 | 0 - 150 |
|-------|---|--------|---------|

See page13 for range of acetabular reamer shells

Minimal invasive acetabular reamer attachment



|       |              |        |         |
|-------|--------------|--------|---------|
| 14990 | Hudson drive | MI-610 | 0 - 150 |
| 15180 | A.O. drive   | MI-610 | 0 - 150 |

See page13 for range of acetabular reamer shells

Minimal invasive acetabular reamer attachment



|       |   |        |         |
|-------|---|--------|---------|
| 11980 | Accepts A.O. radiolucent drill attachment | TX-600 | 0 - 950 |
|-------|---|--------|---------|

Radiolucent drill adaptor



|       |                              |        |                      |
|-------|------------------------------|--------|----------------------|
| 15820 | Accepts P20 series pump kits | LX-620 | 0 - 1600 pulses/min. |
|-------|------------------------------|--------|----------------------|

MPX and MDX handpieces can be connected direct to P20 pump kits. Pulse rate 950 pulses/min when used in this configuration.



Pulse Lavage attachment

|       |                       |        |         |
|-------|-----------------------|--------|---------|
| 16100 | 0.8 - 4.0 mm capacity | WX-620 | 0 - 950 |
|-------|-----------------------|--------|---------|

See Stericut™ catalogue for wires.

Wire/pin driving attachment



**MEDICAL EQUIPMENT SPECIALISTS USA**

2555 N. W. 102 Ave. # 104, Miami, FL 33172 - USA

Tel: 786-401-7719; Fax: 305-501-4786; www.mes-usa.com